# **Solutions from Ruland:** Beam Couplings for Medical Applications



Multiple beam couplings have excellent overall performance characteristics and can easily accommodate shaft misalignment.

Ruland beam couplings utilize two sets of overlapping spiral cuts to increase torque capabilities and torsional rigidity when compared to the commodity style single beam coupling. Separating the spiral cuts into two sets gives the coupling better parallel misalignment capabilities while easily accommodating angular, complex, and axial misalignment. Zero backlash beam couplings are ideally suited for test and measurement, robotics, imaging, patient positioning, liquid chromatography, and lab analysis equipment which require accuracy of motion.

Ruland beam couplings are available with four or six beams in inch, metric, and inch to metric bore combinations ranging from 3/32" (2mm) to 3/4" (20mm). Four beam couplings are more flexible with lower bearing loads while six beam couplings feature a larger body size with shorter spiral cuts to provide increased torque capability, repeatability, and torsional stiffness. Multiple beam couplings are available in aluminum for additional flexibility and low inertia or stainless steel for higher torque and increased corrosion resistance. Special dimensions, spiral cut patterns, finishes, and materials are available by request.

Beam couplings are part of Ruland's complete zero backlash coupling line which includes: rigid, beam, bellows, disc, jaw, and oldham types. All Ruland couplings are manufactured in our Marlborough, Massachusetts factory and are RoHS2 and REACH compliant. Ruland beam couplings are zero backlash, have high torsional stiffness and accommodate misalignment making them well suited for encoder, tachometer, and light duty power transmission applications commonly found in medical equipment. They are designed to ensure low bearing loads and balancing for reduced vibration at higher speeds.



Beam couplings are available in clamp and set screw styles with bore sizes from 3/32" (2mm) to 3/4" (20mm).

#### Why Ruland Beam Couplings?

- Zero backlash for accuracy of motion
- Accommodate all types of misalignment
- Balanced for higher speeds and reduced vibration
- Special designs & materials available on request
- RoHS2 and REACH compliant
- Carefully made in our Marlborough, Massachusetts factory and available for immediate delivery



## www.ruland.com



#### Shaft Collar

Superior fit, finish, and holding power Precise face/bore perpendicularity for proper alignment Steel, aluminum, plastic, 303 & 316 stainless steel



#### **Quick Clamping Shaft Collar**

Designed for quick set up and easy repositioning Innovative clamp design requires no tools Light weight anodized aluminum

## **Rigid Coupling**

Nypatch® anti-vibration hardware Precision honed bores for proper fit and alignment 1 and 2 piece styles with or without keyway

## **Bellows Coupling**

Zero-backlash, aluminum hubs for low inertia Stainless steel bellows for high torsional stiffness Balanced design for speeds up to 10,000 RPM



#### **Beam Coupling**

Zero-backlash, suitable for all types of misalignment Multiple beams for improved torsional rigidity and torque Available in aluminum and stainless steel

## **Oldham Coupling**

Zero-backlash, low bearing loads, low inertia Good overall performance, electrically isolating High parallel misalignment capability

#### **Jaw Coupling**

Zero-backlash, dampens impulse loads Elastomer element in choice of 3 durometers Easily combine inch to metric and keyed to keyless



Zero-backlash, high torsional stiffness Single disc style for compact installations Double disc style for high misalignment







# www.ruland.com